SFM-AT200





The SFM-AT200 can be used to clean parts produced on all additive manufacturing systems.

Compact depowdering unit for powder removal of metal lasermelted parts


The SFM-AT200 cleans metal laser-melted parts within a sealed process chamber, with targeted vibration and automated rotation.

Due to rotation of the parts, including the build plate, unmelted build material is removed from complex voids and support structures.


The compact design of the SFM-AT200 optimizes the footprint as well as the consumption of inert gas.

The internal stainless steel design makes the SFM-AT200 the ideal cleaning system for medical components with high cleaning requirements. The depowdering system is based on the unique Solukon Smart Powder Recuperation® technology.

solukon.de



1160



System specifications

Installation space (W x D x H)	2,200 x 2,400 x 2,200	mm
Weight	150	kg
Mains voltage / frequency	400 / 50 - 60	V / Hz
Power consumption	0.4	kW
Power supply	16	Α
Compressed air specifications		
Working pressure	6	bar
Consumption	max. 300	l/min
Inert gas specifications*		
Working pressure	6	bar

^{*} only with inert gas infusion option

Consumption

Part spectrum

- material: aluminum-, steel-, titan- or copper alloy
- weight: up to 60 kg
- dimensions: up to 300 x 300 x 230 mm³

Basic features

- automated rotation device
- turntable for manual positioning of the parts
- powder lock with special container
- vibration mechanism with wide frequency range

Options

- dust removal for non-reactive materials
- inert gas infusion for reactive materials (ATEX)
- direct link to sieving station

Advantages

- certified explosion protection
- high degree of protection from harmful dusts
- fast and economic part cleaning
- comfortable part handling
- qualifiable and reproducible cleaning results

max. 300 l/min